# **Application Success**

## **Packaging**





## **Application Overview**

High speed filling equipment used to fill large size bladder bags that contain bacterial hand soap.

### Why Automatic Lubrication?

Specialized dispensing source for very expensive NLGI grade 3 food/medical lubricant. Spray nozzle can only handle 70 psi (5 bar) lubricant inlet supply pressure, lubricant application critical to neck area of bladder bag, applying 0.0027cc~(0.00017~cu.~in.) per shot, wasting lubricant is critical in this application, 35 lb pail costs \$3600~each.

## Advantages

- + High level of reliability
- Local distribution and support
- + Wide range of system types to accommodate unique machine arrangements.
- + Positive pump source able to pump heavy grade lubricant consistently
- Distributor added value, the lube package is being supplied on a panel, with electronic monitoring.
- MultiPort is robust and is tried proven pump that can meet customer's expectations: electric, small positive output in consistent fashion, meets budgetary expectations.

## **Products Utilized for Packaging**

#### MultiPort Lubricator

+ **Description:** 24 VDC, 4 liter (8 lb) reservoir, grease, 2 outlet, with a low level switch

The MultiPort Lubricator is a rugged, motor-driven, electric lubricator, equipped with fixed output pumping elements to discharge grease or oil over a wide operating range. Low level switches are standard on this compact unit. Up to three independent feed lines can be used with the MultiPort Lubricator. A selection of timers and controller/monitors are available to program MultiPort Lubricators.



### Typical System Layout

System consisted of a 24 VDC MultiPort Lubricator with two outlets and was controlled by a customer PLC. The Bijur Delimon distributor provided a value added benefit by mounting the MultiPort Lubricator on a panel with an electrical panel enclosure. The assembly was pre-wired. All the customer had to do was bring power to the terminal strip.

## **Background**

This application has resulted in 20 MultiPort Lubricators being sold to the customer. They needed a small amount of a special, very expensive NLGI grade 3 food/medical lubricant applied to the neck of a container bladder bag so that it fit correctly onto a soap filling device. The MultiPort is being used as a positive pump source to prime the inlet of a small spraying/dispensing valve that dispenses 0.0028cc (0.00017 cu. in.) of this lubricant every few seconds.

#### BIJUR DELIMON INTERNATIONAL

(919) 465 4448 LOCAL (800) 631 0168 TOLL-FREE (919) 465 0516 FAX

#### WWW.BIJURDELIMON.COM

2100 Gateway Centre Blvd., Suite 109 Morrisville, NC 27560